



NYS372P-BG

Phono cable jack, gold plated contacts, black plated shell



Technical Information [hide](#)

Product	
Title	NYS372P-BG
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
Mechanical	
Cable O.D.	7.2 mm
Lifetime	> 1000 mating cycles
Wiresize	26 AWG
Material	
Contact plating	Au
Contacts	Brass (CuZn39Pb3)
Shell	Brass (CuZn39Pb3)
Shell plating	Black
Strain relief	SnCe plated, crimp type
Insulation	ABS
Environmental	
Solderability	Complies with IEC 68-2-20

Temperature range

-25 °C to +70 °C

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

REAN[®]
REAN a brand of Neutrik AG