

Signal lamp Tilted Diamond⁺, M12 Terminals, blue

1.69.010.003/1600



General information

Form of lens	round protruding
Cap color/LED color	blue
Diameter of collar	56.9 mm

Dimensions

Overall height	70.01 mm
----------------	----------

Mechanical design

Mounting	2 x screw
Terminals	M12, A-coded, 4-pin
Lamp	4 x LED

Electrical characteristics

Operating voltage U_B	24 V
-------------------------	------

Other specifications

Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+60 °C
Degree of protection from front side	IP 65/67
Weight	65 g
Operating life	50,000 h
ROHS compliant	yes
REACH compliant	yes



