

LUMOTAST 75 IP40 - Signal lamp, square collar, flush lens, housing

1.65.111.061/0000



General information

| | |
|-----------------|--------|
| Form of lens | flat |
| Form of collar | square |
| Color of collar | black |

Dimensions

| | |
|------------------|---------|
| Length of collar | 18 mm |
| Width of collar | 18 mm |
| Overall height | 7.5 mm |
| Mounting depth | 33.5 mm |
| Mounting hole | 16.2 mm |

Mechanical design

| | |
|--------------|---------------------|
| Mounting | ring nut |
| Terminals | solder terminals |
| Lamp socket | T 4.5 |
| Illumination | LED / filament lamp |

Electrical characteristics

| | |
|--------------------|-------|
| Voltage limit max. | 35 V |
| Power limit max. | 1.2 W |

Other specifications

| | |
|--------------------------------------|--|
| Degree of protection from front side | IP40 (DIN EN 60529) |
| Weight | 5 g |
| Operation temperature min. | -25 °C |
| Ambient temp. operating max. | +55 °C |
| Storage temperature min. | -40 °C |
| Storage temperature max. | +80 °C |
| Environmental resistance | acc. to IEC 60068-2-14, -30, -33 and -78 |
| ROHS compliant | yes |
| REACH compliant | yes |

Mounting hole



