

Signal lamps with lamp socket - W 2 x 4.6d, 9.1 mm, housing

1.66.001.026/0000



General information

Form of lens	round
Diameter of collar	11 mm

Dimensions

Overall height	7 mm
Mounting depth	25.5 mm
Mounting hole	9.1 mm

Mechanical design

Mounting	ring nut
Terminals	solder/quick connect terminals 2.8 x 0.8 mm
Lamp socket	W 2 x 4.6d
Lamp	filament lamp

Electrical characteristics

Voltage limit max.	35 V
Power limit max.	1.2 W

Other specifications

Degree of protection from front side	IP40 (DIN EN 60529)
Weight	1 g
ROHS compliant	yes
REACH compliant	yes

Mounting hole

