

RS 76 C - Full-travel key switch, not illuminable

3.13.001.210/0000

Recommended for use of multi-module keycaps.



For accessories and keycaps, refer to RS 76.

General information

Recommended key grid	19.05 mm
----------------------	----------

Mechanical design

Contact function	momentary
Mounting	soldering
Terminals	solder terminals, tin-plated
Contact system	contactless with Hall-IC
Illumination	no

Mechanical characteristics

Switching travel off	0.8 ... 2.4 mm
Operating force max.	1 N
Operating travel	4 mm
Switching travel on	1.5 - 2.8 mm
Robustness max.	100 N

Electrical characteristics

Operating voltage DC	4.75 ... 5.25 V
Supply current max. at $U_{IL} = 0 \text{ V}$	0.5 mA
Supply current max. at $U_{IH} = 5 \text{ V}$	5 mA
Input voltage (F) at $U_{IL} = 0 \text{ V}$	0.4 V
Input voltage (F) at $U_{IH} = 2.4 \text{ V}$	5.25 V
Output load current (Q) max.	16 mA
Output residual current (Q) max.	10 μA
Output saturation voltage (Q) max. bei 16 mA	0.4 V
ESD strength max.	8 kV
Output switching times (Q) at 25 °C, t_{PHL}	3 μs
Output switching times (Q) at 25 °C, t_{PLH}	4 μs
Output switching times (Q) at 25 °C, t_{THL}	1 μs
Output switching times (Q) at 25 °C, t_{TLH}	2 μs

Other specifications

Reliability of Hall-IC at 25 °C	$\lambda = 2.5 \times 10^{-7} \text{ h}^{-1}$
Ambient temp. operating min.	0 °C
Ambient temp. operating max.	+70 °C
Storage temperature min.	-40 °C
Storage temperature max. (product)	+80 °C
Storage temperature max. (rail)	+50 °C
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
Operating life min. (operations)	10^8 cycle
Degree of protection	IP40 (DIN EN 60529)
Flammability of materials	UL 94 HB
ROHS compliant	yes
REACH compliant	yes

