

REDINGTON COUNTERS, INC.
P.O. Box 608, 130 Addison Road, Windsor, CT 06095
Toll Free: (860) 688-6205 • Fax: 860/688-1591
E-Mail: Info@RedingtonCounters.com • Website: www.RedingtonCounters.com

Item # 5300-1000, Beige Case



Beige Case

The Model 53 Electronic Totalizer with 7 or 8 LCD digits is ideal as a replacement for electromechanical totalizers or where external power is not available. Powered by an internal lithium battery these products are highly reliable and provide the user with a choice of several options; with or without reset and multiple count ranges for optimized performance. The case is available in either tan or black.

SPECIFICATIONS

Model No.	53
Mounting	Panel with clip
Display	7 8 LCD figures, 0.32 inch (8mm) high
Display Height	0.32 Inch
Display Height	8 mm
No. of Digits	7
Vih	20VAC/3VDC min.
Vil	3VAC/1VDC max.
Input	3-30 VDC
Battery	Self-powered (internal lithium battery)
Battery Life	20 years (approx.)
Reset Type	Remote
Speed	0-40 counts/second (min. 12.5ms - on, 12.5ms - off), 0-150 counts/second (min. 3.3ms - on, 3.3ms - off)
Shock	Operating: 10G, Non-operating: 30G
Vibration	Operating: 10 to 55 Hz. 0.01 inch (0.25mm) double amplitude, Non-operating: 10 to 55 Hz. 0.03 inch (0.75mm) double amplitude
Humidity	0 to 95% RH, non-condensing
Operating Temperature	-4 to +140 °F
Operating Temperature	-20 to +60 °C
Storage Temperature	-40 to +165 °F

Storage Temperature	-40 to +75 °C
Approvals	UL Recognized, CSA Certified, CE Compliant
Termination	Terminal block
Weight	2 oz
Weight	57 gm
Dielectric	1000VAC 50/60Hz for 1 minute
Accuracy	100% (Provided Signal Meets Stated Parameters)
Color	Tan
Stock Availability	Yes