

Data sheet

REGplus IP20 E2000 DC MM H+S

Page 1/4

P/N

130F5A7003-E

EAN 4250184149934

2015-07-07

Illustrations



Product specification

- termination with an E2000 DC coupler for mounting on TH35 rail to DIN EN 60715
- slotted zirconium oxide ceramics sleeve (ZrO₂)
- high material stability and surface quality and long service life
- service life: min. 1000 plug cycles
- cable feed 45° from the top, plug direction 45° downwards
- width of 1HP allows mounting up to 12 REG in standard electrical distribution panels
- to install the coupler, the existing dust protection cover must be removed
- variants: blue (SM), green (SM APC), beige (MM)



Data sheet
REGplus IP20 E2000 DC MM H+S

Page 2/4

P/N
130F5A7003-E
EAN 4250184149934

2015-07-07

Technical Data

General Data

Fields of application	Office
Design	Wall outlet
Mounting style	Standard rail TH35
Transmission technology	Fiber optic
Color	light gray
Dimensions	
Dimension (L x W x H)	83.30 x 17.50 x 60.00 mm
Dimension (L x W x H)	3.28 x 0.69 x 2.36 in.
Horizontal pitch	1 TE
Mode type of the fiber	Multimode
Labeling option	label window with identification label
Marking option	by dust protection

Connections/interfaces

Connector technology interface 1	E2000 DC
Connector technology interface 2	E2000 DC
Number of ports interface 1	1
Number of ports interface 2	1
Number of equipped ports interface 1	1
Number of ports interface 2 equipped	1
Number of ports with dust protection interface 1	1
Number of ports with dust protection interface 2	1
Module plug-in direction	45° downwards
Cable access/outlet	45° from the top

Mechanical characteristics

Cut-out	E2000 DC
Connector type	Duplex
Position/mounting of latch - standard installation position	top

Data sheet
REGplus IP20 E2000 DC MM H+S

Page 3/4

P/N
130F5A7003-E
EAN 4250184149934

2015-07-07

Technical Data

Materials and material properties

Material - Housing	Plastics
Material - Cover part(s)	Frianyl
Material - Lower housing	Frianyl
Material - Label window	ABS, transparent
Material - Sleeve	PhBr, slotted

Environmental conditions

Temperature (min. - max.)	
Temperature - Storage °C	-40 - 70 °C
Temperature - Storage °F	-40 - 158 °F
Temperature - Operating °C	-40 - 70 °C
Temperature - Operating °F	-40 - 158 °F
Increased robustness	yes

Certifications

Gost Certification	yes
RoHS	compliant

Classifications

ETIM 5.0	EC001130
----------	----------

Packing details

Type of packaging	1 pc(s) / plastic bag
Packaging unit - Weight (gram)	51.00 g
Packaging unit - Weight (pound)	0.11 lb

© 2015 METZ CONNECT - Technische Änderungen vorbehalten! Subject to modifications! Sous réserve de modifications techniques!



Data sheet
REGplus IP20 E2000 DC MM H+S

Page 4/4

P/N
130F5A7003-E
EAN 4250184149934

2015-07-07

Accessories

P/N	Designation
899011-01	Label sheet for Modul patch panels / REG

