

Data sheet

REGplus IP20 E2000 DC SM H+S

Page 1/4

P/N

130F5B7003-E

EAN 4250184149927

2015-07-07

Illustrations



Product specification

- termination with an E2000 DC coupler for mounting on TH35 rail to DIN EN 60715
- slotted zirconium oxide ceramics sleeve (ZrO2)
- high material stability and surface quality and long service life
- service life: min. 1000 plug cycles
- cable feed 45° from the top, plug direction 45° downwards
- width of 1HP allows mounting up to 12 REG in standard electrical distribution panels
- to install the coupler, the existing dust protection cover must be removed
- variants: blue (SM), green (SM APC), beige (MM)

Data sheet
REGplus IP20 E2000 DC SM H+S

Page 2/4

P/N
130F5B7003-E
EAN 4250184149927

2015-07-07

Technical Data

General Data

| | |
|-------------------------|--|
| Fields of application | Office |
| Design | Wall outlet |
| Mounting style | Standard rail TH35 |
| Transmission technology | Fiber optic |
| Color | light gray |
| Dimensions | |
| Dimension (L x W x H) | 83.30 x 17.50 x 60.00 mm |
| Dimension (L x W x H) | 3.28 x 0.69 x 2.36 in. |
| Horizontal pitch | 1 TE |
| Mode type of the fiber | Single mode |
| Labeling option | label window with identification label |
| Marking option | by dust protection |

Connections/interfaces

| | |
|--|------------------|
| Connector technology interface 1 | E2000 DC |
| Connector technology interface 2 | E2000 DC |
| Number of ports interface 1 | 1 |
| Number of ports interface 2 | 1 |
| Number of equipped ports interface 1 | 1 |
| Number of ports interface 2 equipped | 1 |
| Number of ports with dust protection interface 1 | 1 |
| Number of ports with dust protection interface 2 | 1 |
| Module plug-in direction | 45° downwards |
| Cable access/outlet | 45° from the top |

Mechanical characteristics

| | |
|---|----------|
| Cut-out | E2000 DC |
| Connector type | Duplex |
| Position/mounting of latch - standard installation position | top |



Data sheet
REGplus IP20 E2000 DC SM H+S

Page 3/4

P/N
130F5B7003-E
EAN 4250184149927

2015-07-07

Technical Data

Materials and material properties

| | |
|--------------------------|------------------|
| Material - Housing | Plastics |
| Material - Cover part(s) | Frianyl |
| Material - Lower housing | Frianyl |
| Material - Label window | ABS, transparent |
| Material - Sleeve | ceramic, slotted |

Environmental conditions

| | |
|----------------------------|--------------|
| Temperature (min. - max.) | |
| Temperature - Storage °C | -40 - 70 °C |
| Temperature - Storage °F | -40 - 158 °F |
| Temperature - Operating °C | -40 - 70 °C |
| Temperature - Operating °F | -40 - 158 °F |
| Increased robustness | yes |

Certifications

| | |
|--------------------|-----------|
| Gost Certification | yes |
| RoHS | compliant |

Classifications

| | |
|----------|----------|
| ETIM 5.0 | EC001130 |
|----------|----------|

Packing details

| | |
|---------------------------------|-----------------------|
| Type of packaging | 1 pc(s) / plastic bag |
| Packaging unit - Weight (gram) | 51.00 g |
| Packaging unit - Weight (pound) | 0.11 lb |



Data sheet
REGplus IP20 E2000 DC SM H+S

Page 4/4

P/N
130F5B7003-E
EAN **4250184149927**

2015-07-07

Accessories

| P/N | Designation |
|-----------|--|
| 899011-01 | Label sheet for Modul patch panels / REG |

