

## Data sheet

### OpDAT REGpro front cover 3RU, 7HP 6xQ-LC MM (Ph-Br, beige)

P/N  
15024A7206-E


EAN 4250184161110

2015-28-05

## Illustrations



Dimensional drawing



See enlarged drawings at the end of document

## Product specification

- front plate 3RU/7HP Q-LC couplers
- slotted ceramics sleeve for single mode applications
- slotted metal sleeve (Ph-Br) for multi mode applications
- suitable for mounting in OpDAT REGpro and OpDAT REGpro24
- gray, powder-coated steel sheet
- variants: 6xQ-LC (blue), 3xQ-LC (heather violet), 6xQ-LC (heather violet), 6xQ-LC (aqua), 3xQ-LC (beige), 6xQ-LC (beige)

## Technical Data

### General Data

Fields of application	Structured building cabling
Design	Front cover
Mounting style	3RU/7HP
Transmission technology	Fiber optic
Color	beige
Dimensions	
Dimension (L x W x H)	30.70 x 128.90 x 35.30 mm
Dimension (L x W x H)	1.21 x 5.07 x 1.39 in.
Height unit	3RU
Horizontal pitch	7Units
Mode type of the fiber	Multimode
Special features	Connection technology: for fusion splice or pre-assembled cable

### Connections/interfaces

Connector technology interface 1	LC-Q Couplers
Connector technology interface 2	LC-Q Couplers
Number of ports interface 1	6
Number of ports interface 2	6
Number of equipped ports interface 1	6
Number of ports interface 2 equipped	6
Number of ports with dust protection interface 1	6
Number of ports with dust protection interface 2	6

### Mechanical characteristics

Cut-out	SC-D, LC-Q, ST-D
Life - Number of mating cycles	min. 500

### Materials and material properties

Material - Coupler housing	Plastics
Material - Mounting plate	steel
Material - Mounting plate finish	powder-coated
Material - Sleeve	PhBr, slotted

## OpDAT REGpro front cover 3RU, 7HP 6xQ-LC MM (Ph-Br, beige)

P/N

15024A7206-E

EAN 4250184161110

2015-28-05

### Technical Data

#### Certifications

Gost Certification yes

#### Approvals

RoHS compliant

#### The product meets the following standards

Fibre optic connector interfaces DIN EN 61754-20

#### Classifications

ETIM 5.0 EC001130

#### Packing details

Type of packaging	10 pc(s) / box
Packaging unit - Weight (gram)	280.00 g
Packaging unit - Weight (pound)	0.62 lb
Packaging dimension (W x H x D)	205.00 x 105.00 x 89.00 mm
Packaging dimension (W x H x D)	8.07 x 4.13 x 3.50 in.



Illustrations

Dimensional drawing

