

Data sheet

OpDAT fix patch panel 12xLC-D (Ph-Br, beige), cable divider

P/N

1502507312-E


EAN 4250184126546

2015-28-05

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- 19 inch 1RU fiber optic patch panel for fixed installation
- light aluminum construction with steel sheet front plate painted in RAL 7035
- equipped with LC-D couplers
- unoccupied recesses are closed with blind plugs
- removable front plate for easy adapter mounting
- screwed on cover for easy access during service work
- several possibilities for cable entry on the back (fastening with PG13.5, PG16 and PG21 or M20 and M25)
- toolless fastening of pre-assembled installation cables (OpDAT VIK) in a U-shaped cutout
- variants: equipped with 6, 12 or 24 LC-D adapters, all blue (SM), heather violet (OM4), aqua (OM3) or beige (MM)



OpDAT fix patch panel 12xLC-D (Ph-Br, beige), cable divider

P/N

1502507312-E

EAN 4250184126546

2015-28-05

Technical Data

General Data

Fields of application	Structured building cabling, Data center
Design	patch panel
Mounting style	1RU
Transmission technology	Fiber optic
Port numbering	yes
Color	aqua
Dimensions	
Dimension (L x W x H)	242.50 x 482.60 x 44.45 mm
Dimension (L x W x H)	9.55 x 19.00 x 1.75 in.
Inches	19 inches
Height unit	1RU
Installation depth	240.00 mm
Installation depth	9.45 in.
Mode type of the fiber	Multimode

Connections/interfaces

Connector technology interface 1	LC-D Couplers
Connector technology interface 2	LC-D Couplers
Number of ports interface 1	24
Number of ports interface 2	24
Number of equipped ports interface 1	12
Number of ports interface 2 equipped	12
Number of ports with dust protection interface 1	12
Number of ports with dust protection interface 2	12
Number of blind covers interface 2	12
Cable access/outlet	several possibilities for cable entry on the back

Mechanical characteristics

Cut-out	SC, LC-D, E2000
Connector type	Duplex
Life - Number of mating cycles	min. 500

OpDAT fix patch panel 12xLC-D (Ph-Br, beige), cable divider

P/N

1502507312-E

EAN 4250184126546

2015-28-05

Technical Data

Materials and material properties

Material - Coupler housing	Plastics
Material - Front cover	sheet steel
Material - Sleeve	PhBr, slotted

Certifications

Gost Certification	yes
--------------------	-----

Approvals

RoHS	compliant
------	-----------

The product meets the following standards

Fibre optic connector interfaces	DIN EN 61754-20
----------------------------------	-----------------

Classifications

ETIM 5.0	EC001130
----------	----------

Packing details

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	1560.00 g
Packaging unit - Weight (pound)	3.44 lb
Packaging dimension (W x H x D)	580.00 x 405.00 x 70.00 mm
Packaging dimension (W x H x D)	22.83 x 15.94 x 2.76 in.



Illustrations

Dimensional drawing

