

Data sheet

OpDAT fix patch panel 24xLC-D (Ph-Br, beige), cable divider

P/N

1502507324-E


EAN 4250184126805

2015-28-05

Illustrations



Dimensional drawing



See enlarged drawings at the end of document

Product specification

- 19 inch 1RU fiber optic patch panel for fixed installation
- light aluminum construction with steel sheet front plate painted in RAL 7035
- equipped with LC-D couplers
- unoccupied recesses are closed with blind plugs
- removable front plate for easy adapter mounting
- screwed on cover for easy access during service work
- several possibilities for cable entry on the back (fastening with PG13.5, PG16 and PG21 or M20 and M25)
- toolless fastening of pre-assembled installation cables (OpDAT VIK) in a U-shaped cutout
- variants: equipped with 6, 12 or 24 LC-D adapters, all blue (SM), heather violet (OM4), aqua (OM3) or beige (MM)

Technical Data

General Data

Fields of application	Structured building cabling, Data center
Design	patch panel
Mounting style	1RU
Transmission technology	Fiber optic
Port numbering	yes
Color	aqua
Dimensions	
Dimension (L x W x H)	242.50 x 482.60 x 44.45 mm
Dimension (L x W x H)	9.55 x 19.00 x 1.75 in.
Inches	19 inches
Height unit	1RU
Installation depth	240.00 mm
Installation depth	9.45 in.
Mode type of the fiber	Multimode

Connections/interfaces

Connector technology interface 1	LC-D Couplers
Connector technology interface 2	LC-D Couplers
Number of ports interface 1	24
Number of ports interface 2	24
Number of equipped ports interface 1	24
Number of ports interface 2 equipped	24
Number of ports with dust protection interface 1	24
Number of ports with dust protection interface 2	24
Cable access/outlet	several possibilities for cable entry on the back

Mechanical characteristics

Cut-out	SC, LC-D, E2000
Connector type	Duplex
Life - Number of mating cycles	min. 500

Technical Data

Materials and material properties

Material - Coupler housing	Plastics
Material - Front cover	sheet steel
Material - Sleeve	PhBr, slotted

Certifications

Gost Certification	yes
--------------------	-----

Approvals

RoHS	compliant
------	-----------

The product meets the following standards

Fibre optic connector interfaces	DIN EN 61754-20
----------------------------------	-----------------

Classifications

ETIM 5.0	EC001130
----------	----------

Packing details

Type of packaging	1 pc(s) / box
Packaging unit - Weight (gram)	1590.00 g
Packaging unit - Weight (pound)	3.51 lb
Packaging dimension (W x H x D)	580.00 x 405.00 x 70.00 mm
Packaging dimension (W x H x D)	22.83 x 15.94 x 2.76 in.



Illustrations

Dimensional drawing

