

[Industrial Products](#) >
 [Jacks and Plugs](#) >
 [1/4" Jacks and Plugs](#) >
 [1/4" Right Angle Open Frame Jack](#)

1/4" Right Angle Open Frame Jack

Long spring design reliability with minimum behind - panel depth. Series 50 same as Series 20, except solder lug location requires more depth, but less panel space. Number C55B has MIL type insulation and finish.

[enlarge](#)

Need more info? [Contact Switchcraft customer service](#)

Product	Description	Typical Mating	Layout	Drawings	Distributor Inventory	
24BX	3 Conductor, short frame right angle jack	267	XII		check stock	
25X	1/4" Right Angle Open Frame Jack, 2 conductor	250	XIII		check stock	
53B	1/4" Right Angle Open Frame Jack, 3 conductor	267	VII		check stock	⌚
54A	1/4" Right Angle Open Frame Jack, 2 conductor	250	XI		check stock	⌚
54B	1/4" Right Angle Open Frame Jack, 3 conductor	267	XII		check stock	⌚
55	1/4" Right Angle Open Frame Jack, 2 conductor	250	XIII		check stock	⌚
C55B	1/4" Shielded Jack 3 -conductor, MIL Type JJ -095, M641/14 -1	482	XV		check stock	⌚

⌚ denotes a special order