

Home > Industrial Products > Jacks and Plugs > 1/4" Jacks and Plugs > 1/4" Long Frame Jacks and Plugs > 1/4" Long Frame Jack

1/4" LONG FRAME JACK



Long frame jacks are designed especially for high quality communication equipment, and to meet exacting MIL specifications, as well as telephone and communication systems. Many jacks have WEco equivalent types. MT-Jax® phone jacks are offered in four styles: MT-Jax, WMT-Jax®, XMT-Jax® and YMT-Jax®. Rugged steel frames are produced in specially designed dies, press welded to provide rigidity and dimensional stability required by telephone and communication jack panels - and to meet MIL frame strength tests. "A" and "C" frame styles are available.

Questions? Contact Switchcraft Customer Support at 1-773-792-2700

Product	Description	
CMT334F	2-conductor 1/4" Long Frame Jack, WEco Equiv. 226C, Max. Diameter "x" 0.562" (14.3mm) read more >>	BUY
CMT336	3-conductor 1/4" Long Frame Jack, WEco Equiv. 241C, Max. Diameter "x" 0.562" (14.3mm) read more >>	BUY
CMT336A	3-conductor 1/4" Long Frame Jack, WEco Equiv. 242C, Max. Diameter "x" 0.688" (17.5mm) read more >>	PDF BUY IN STOCK
CMT336B	3-conductor 1/4" Long Frame Jack, WEco Equiv. 285C, Max. Diameter "x" 0.812" (20.6mm) read more >>	BUY IN STOCK
CMT336C	3-conductor 1/4" Long Frame Jack, WEco Equiv. 240C, Max. Diameter "x" 0.688" (17.5mm) read more >>	PDF BUY
CMT346	3-conductor 1/4" Long Frame Jack, WEco Equiv. 249C, Max. Diameter "x" 0.562" (14.3mm) read more >>	BUY
MT331X	2-conductor 1/4" Long Frame Jack, WEco Equiv. 233A or 221E3, MIL Type M641/2-8, Max. Diameter "x" 0.428" (11.1mm) read more >>	PDF BUY IN STOCK
MT332AX	2-conductor 1/4" Long Frame Jack, WEco Equiv. 218A, MIL Type M641/2-3, Max. Diameter "x" 0.5" (12.7mm) read more >>	PDF BUY
MT332BX	3-conductor 1/4" Long Frame Jack, WEco Equiv. 238A, MIL Type M641/3-1, Max. Diameter "x" 0.562" (14.3mm) read more >>	PDF BUY IN STOCK
MT333BX	3-conductor 1/4" Long Frame Jack, WEco Equiv. 300A, Max. Diameter "x" 0.562" (14.3mm) read more >>	BUY










Downloads:

[Jack Schematics](#)
[Specification Sheet](#)

Associated Products:



1/4" Longframe Audio Plug

MT333X		2-conductor 1/4" Long Frame Jack, WEco Equiv. 215A, MIL Type M641/2-6, Max. Diameter "x" 0.469" (11.9mm) read more >>		BUY	IN STOCK
MT334BX		3-conductor 1/4" Long Frame Jack, WEco Equiv. 239AM, MIL Type M641/3-2, Max. Diameter "x" 0.562" (14.3mm) read more >>		BUY	IN STOCK
MT334F		2-conductor 1/4" Long Frame Jack, WEco Equiv. 226A, MIL Type M641/2-4, Max. Diameter "x" 0.562" (14.3mm) read more >>		BUY	IN STOCK
MT336		3-conductor 1/4" Long Frame Jack, WEco Equiv. 241A, MIL Type M641/3-4, Max. Diameter "x" 0.562" (14.3mm) read more >>		BUY	
MT342B		3-conductor 1/4" Long Frame Jack, WEco Equiv. 246A, Max. Diameter "x" 0.563" (14.3mm) read more >>		BUY	
MT343B		3-conductor 1/4" Long Frame Jack, Max. Diameter "x" 0.5" (12.7mm) read more >>		BUY	
MT344B		3-conductor 1/4" Long Frame Jack, WEco Equiv. 248A, Max. Diameter "x" 0.625" (15.9mm) read more >>		BUY	
MT346		3-conductor 1/4" Long Frame Jack, WEco Equiv. 249A, Max. Diameter "x" 0.562" (14.3mm) read more >>		BUY	
MT346A		3-conductor 1/4" Long Frame Jack, Max. Diameter "x" 0.688" (17.5mm) read more >>		BUY	
MT346B		3-conductor 1/4" Long Frame Jack, Max. Diameter "x" 0.812" (20.6mm) read more >>		BUY	
MT346C		3-conductor 1/4" Long Frame Jack, Max. Diameter "x" 0.688" (17.5mm) read more >>		BUY	
WMT332BX		3-conductor 1/4" Long Frame Jack, WEco Equiv. 238AM, Max. Diameter "x" 0.562" (14.3mm) read more >>		BUY	
WMT334BX		3-conductor 1/4" Long Frame Jack, WEco Equiv. 239AM, Max. Diameter "x" 0.578" (14.7mm) read more >>		BUY	