

Right Angle Connector EMC with positioning, for cable 7-12 mm 7.301.500.000

cable diameter	7 – 12 mm
Housing material	Copper-Zinc alloy, Die Cast
Operating-Temperature	-40 – 125 °C
Protection category	IP67/ IP69K plugged
Seals / O-Rings	Buna-N standard
Surface material	Nickel

[REQUEST 3D DATA](#)

Certificates [i](#)

[ADD TO WATCHLIST](#)

[PRINT](#)

SUPPORT

Additional information

// [Assembly instruction EMC Righth Angle Panel Connector](#)

ELECTRIC COMPONENTS

- Circular Connectors
- Industrial Cable Glands
- Industrial Ex Cable Glands
- "Hazardous Areas" Cable Glands
- Conduit Systems
- Customized Projects

HEATING EQUIPMENT

- Problem Fixer
- Fittings
- Designtechnic
- Accessories, Spare Parts, Tools

INFORMATION

- News
- Imprint
- Privacy Policy
- GTC

NEWSLETTER

[SUBSCRIBE TO NEWSLETTER](#)