

Multiple cable insertion HSK-ME 1.089.2100.19

Multi hole inserts for HSK-Industry Standard liquid tight strain relief fittings

Fits to AG	3/4 npt
Material	Elastomer
Number of Holes x d	4 x 6
Operating-Temperature	-40 – 100 °C


Advice:

- // The shown inserts are samples, more inserts upon request.
- // The inserts are exclusively capable for the glands of the HSK series




[DOWNLOAD 3D DATA](#)

Certificates [i](#)



[ADD TO WATCHLIST](#)

[PRINT](#)

SUPPORT 

ELECTRIC COMPONENTS

- Circular Connectors
- Industrial Cable Glands
- Industrial Ex Cable Glands
- "Hazardous Areas" Cable Glands
- Conduit Systems
- Customized Projects

HEATING EQUIPMENT

- Problem Fixer
- Fittings
- Designtechnic
- Accessories, Spare Parts, Tools

INFORMATION

- News
- Imprint
- Privacy Policy
- GTC

NEWSLETTER

[SUBSCRIBE TO NEWSLETTER](#)