

# Multiple cable insertion HSK-ME

## 1.089.1602.19

Multi hole inserts for HSK-Industry Standard liquid tight strain relief fittings


<b>Fits to AG</b>	1/2 npt/16
<b>Material</b>	Elastomer
<b>Number of Holes x d</b>	4 x 4
<b>Operating-Temperature</b>	-40 – 100 °C


Advice:

- // The shown inserts are samples, more inserts upon request.
- // The inserts are exclusively capable for the glands of the HSK series




[DOWNLOAD 3D DATA](#)

Certificates 



[ADD TO WATCHLIST](#)

[PRINT](#)

SUPPORT 

### ELECTRIC COMPONENTS

- Circular Connectors
- Industrial Cable Glands
- Industrial Ex Cable Glands
- "Hazardous Areas" Cable Glands
- Conduit Systems
- Customized Projects

### HEATING EQUIPMENT

- Problem Fixer
- Fittings
- Designtechnic
- Accessories, Spare Parts, Tools

### INFORMATION

- News
- Imprint
- Privacy Policy
- GTC

### NEWSLETTER

[SUBSCRIBE TO NEWSLETTER](#)