


HSK-K-MULTI-Ex-Active Metric 1.581.2501.51


Multi-hole liquid tight strain relief fittings made of nylon 6/6


colour	black
Ex-protection level	II 2G Ex eb IIC Gb / II 1D Ex ta IIIC Da
Height	31 mm
Male thread	M 25 x 1,5
Material	Polyamide, fiber reinforced
Number of Holes x d	3 x 7
O-Ring	Buna-N
Operating-Temperature	-20 – 85 °C
Protection category	IP 68 - 10 bar within the specific clamping range
Seal	Elastomer
Thread Length	11 mm
Wrench size	33 mm


- Advice:
- // O-Ring FKM and VMQ upon request
 - // These inserts are examples, other inserts available upon request
 - // Installation note: The cable diameter may be less than the drill diameter by 20%, but not more than 1 mm.



[REQUEST 3D DATA](#)


Certificates 


RoHS


SP


ATEX


ATEX


IECEx

ATEX

ATEX

 [ADD TO WATCHLIST](#)

 [PRINT](#)

SUPPORT 

ELECTRIC COMPONENTS

- Circular Connectors
- Industrial Cable Glands
- Industrial Ex Cable Glands
- "Hazardous Areas" Cable Glands
- Conduit Systems
- Customized Projects

HEATING EQUIPMENT

- Problem Fixer
- Fittings
- Designtechnic
- Accessories, Spare Parts, Tools

INFORMATION

- News
- Imprint
- Privacy Policy
- GTC

NEWSLETTER

[SUBSCRIBE TO NEWSLETTER](#)

This website uses cookies to ensure you get the best experience on our website.

OK