

Accessory / spare part, for plastic/metal range, round, 22 mm, 26x26mm, Lamp with base BA9s, incandescent lamp, 2.6 W, Length max. 28 mm, Piston diameter 10 mm, rated voltage, 110/130 V AC/DC, clear



Figure similar

General technical data:		
Product designation		incandescent lamp
Type of light source		filament lamp
Color of the light source		clear
Mounting type		BA 9s
Product component		
• series resistor		No
• diode		No
• lamp transformer		No
• Light source		Yes
Type of voltage for actuation		AC/DC
Operating voltage		
• at AC		
— at 50 Hz rated value	V	110 ... 130
— at 60 Hz rated value	V	110 ... 130
• at DC rated value	V	110 ... 130

Consumed current for rated value of supply voltage maximum	mA	25
Type of electrical connection		Miscellaneous
Mounting type		miscellaneous

Certificates/approvals

General Product Approval

other

[Confirmation](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SX1731>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SX1731>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SX1731>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SX1731&lang=en

last modified:

09/12/2019