



Ordering Information

- ▶ Accessories see pages 516–521.
- ▶ Enclosures see page 523.
- ▶ Dimensions see pages 529–533.


Double Pushbutton Actuator with Holder

Image	Description	Catalog No	Price \$	
 Double Pushbutton	Double pushbuttons IP 65 with flush and raised buttons	green/red inscription I/O	3SB3100-8CC21	19.90
	with flush buttons		3SB3100-8AC21	19.90
	Double pushbuttons with indicator light , IP 65 with flush and raised buttons, incl. holder for 3 elements	green/red inscription I/O	3SB3101-8DC21	25.50
	with flush buttons		3SB3101-8BC21	25.50


Accessories—Double Pushbuttons

Image	Description	Catalog No	Price \$
 Protective Cap	Holder 30 mm × 70 mm for inscription plate 12.5 mm × 27 mm	3SB3922-0AY	1.20
	Protective cap , Silicone for degree of protection IP 67 can be used for double pushbutton with flush buttons	3SB3921-0AQ	7.70

Audible Signals—Complete Units

Image	Description	Catalog No	Price \$	
 Audible Signal Device	Audible signal device, IP 65 black	Operational voltage 24V AC/DC	3SB3233-7BA10	58.00
	Continuous tone (2.4 kHz)	115V AC/DC	3SB3234-7BA10	58.00
	Operational current min. 10 mA	230V AC/DC	3SB3235-7BA10	58.00
	Sound pressure level min. 80 dB/10 cm			

Audible Signals

Image	Description	Catalog No	Price \$	
 Audible Signal Transformer	Audible signal device, IP 40 [ⓐ] black for audible signal transformer with holder	3SB3000-7AA10	15.40	
	Audible signal transformer for audible signal device Base BA 9s	24 to max. 28V DC	3SB1902-2BN	23.00
	Operational current 25 mA, 0.6W Noise level min 80 dB/10 cm			
	Lampholder	3SB3400-1A	16.70	

[ⓐ] Audible signal and lampholder must be ordered separately.