



Siemens Low Voltage's Multi-Family Metering Line of PAK Metering: EUSERC as part of the PAK Metering: EUSERC Group. Type: UNI-PAK Features: NO BYPASS EUSERC CERTIFIED Appn: GARDEN - STYLE Std: UL-50,67,414 V. Rating: 120/240V A. Rating: 200A Phase: 1PH Size: 7.25 x 14.05 x 33.380 No. Of Cutouts: 7 Cutout Size: 2X1/2", 1 x (1-1/2, 1-1/4, 1"), 2 x (2, 1-1/2, 1-1/4, 1"), 1 x (3, 2-1/2, 2, 1-1/2, 2"), 1X4" Cable Entry: TOP OR BOTTOM FEED Terminal: 3X2 STUDS. Insulated. Appn.: Wall Mounted. Enclosure: RING

cable entry type	TOP OR BOTTOM FEED
fastening method	WALL MOUNTED
suitability for operation	GARDEN-STYLE
Electricity	
ampacity	200 A
Model	
product brand name	Siemens
product type designation	UNI-PAK
special product feature	NO BYPASS EUSERC CERTIFIED
Mechanical Design	
design of the terminal strip	3X2 STUDS
General product approval	
certificate of suitability	UL-50;67;414

last modified: 3/19/2020 

