

## 9007AP303

9007 snap switch - parallel roller plunger operator -  
bushing mount - oiltight



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Snap limit switch operator
Device short name	9007AO/CO

### Complementary

Operator profile	Plunger head
Fixing mode	By the head
Movement of operating head	Linear
Product compatibility	Snap basic limit switch
Type of operator	Steel spring return roller plunger
Switch actuation	By 30° cam
Type of approach	2 directions traverse approach
Width	0.83 in
Height	2.5 in
Depth	1.6 in
Product weight	0.1 lb(US)

### Environment

NEMA degree of protection	NEMA 1 conforming to Nema type 250
IP degree of protection	IP20 conforming to IEC 60529
Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F

### Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.