

Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007A 9007B 9007C 9007N 9007T10 9007T5
Associated complete product	9007AW 9007C
Movement of operating head	Rotary
Type of operator	Cast zinc spring return 360° adjustable roller lever length: 1.38 in - offset: - ball bearing roller to pass over switch cover
Type of roller	1 steel outside roller (convertible) diameter: 0.69 in - width: 0.25 in
Type of approach	Lateral approach
Positive opening	Without

Complementary

Switch actuation	By 30° cam
Product weight	0.24 lb(US)

Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.