

Main

| | |
|-----------------------------|---|
| Range of product | L100/300 |
| Series name | Severe duty |
| Product or component type | Limit switch lever |
| Device short name | L100/300 |
| Associated complete product | HL100 HL300 HML100 HML300 L100 L300 ML100 ML300 |
| Movement of operating head | Rotary |
| Type of operator | Aluminium spring return 360° adjustable roller lever length: 2.5 in - offset: - to pass over switch cover |
| Type of roller | 1 steel outside roller diameter: 0.75 in - width: 0.25 in |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Product weight | 0.1 lb(US) |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -20...185 °F |
| Ambient air temperature for storage | -20...185 °F |
| Environmental characteristic | Standard environment |

Contractual warranty

| | |
|--------|-----------|
| Period | 18 months |
|--------|-----------|