


DATE	REV	ECN	APP'D. BY
05/17/17	A0	Released	HU
08/07/17	A1	11059	KC
12/03/19	A2	11479	ADB



Notes:

- Each cable assembly to be individually bagged.
- 50μ" Gold plating on contacts
- Cable Construction:
 - 24AWG Stranded T/C
 - 4Pr, U/UTP, Type CMG
 - PVC Jacket
- Overmolded Strain Relief
Color to match Jacket color

P/N Key:

BC-5Uxxxxyz

UOM

M = Meters
F = Feet

Length

Meters = xx.x (00.3 - 30.0)
Feet = xxx (001 - 100)

Color

E = Blue O = Orange
G = Grey R = Red
K = Black W = White
N = Green Y = Yellow

O/A Length Tolerance:


Metric

0 ~ 200mm ±10mm
201 ~ 1000mm ±20mm
1001 ~ 1500mm ±25mm
1501 ~ 2100mm ±30mm
>2100mm ±40mm

Imperial

0 ~ 1ft ±0.5in
2ft ~ 3ft ±0.75in
4ft ~ 7ft ±1.0in
> 7ft ±1.5in

Wiring Map: 568B Standard




Example Parts Numbers

Feet		
P/N	Color	Length
BC-5UG001F	Grey	1'
BC-5UK010F	Black	10'
BC-5UE050F	Blue	50'

Meters		
P/N	Color	Length
BC-5UG005M	Grey	0.5m
BC-5UE010M	Blue	1.0m
BC-5UE050M	Blue	5.0m


For Part Numbers Not Shown Follow Part Number Key Format



DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]
UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°

SHEET NO. 1 OF 1



bel

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE:

Bel Patchcord Assembly, C5e U/UTP

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF BEL FUSE, INC.

DRN BY:	XYQ	DATE	05/17/17
APPD BY:	HU	DATE	05/17/17
DWG NO.	CT999139	REV.	A2