


DATE	REV	ECN	APP'D. BY
05/17/17	A0	Released	HU
08/07/17	A1	11059	KC
12/03/19	A2	11479	ADB



Notes:

- Each cable assembly to be individually bagged.
- 50 μ " Gold plating on contacts
- Cable Construction:
 - 24AWG Stranded
 - 4Pr, U/UTP, Type CMG
 - PVC Jacket
- Overmolded Strain Relief
Color to match Jacket color

P/N Key:

BC-6Uxyyyz

UOM

M = Meters
F = Feet

Length

Meters = xx.x (00.3 - 30.0)
Feet = xxx (001 - 100)

Color

E = Blue O = Orange
G = Grey R = Red
K = Black W = White
N = Green Y = Yellow

O/A Length Tolerance:


Metric

0 ~ 200mm ±10mm
201 ~ 1000mm ±20mm
1001 ~ 1500mm ±25mm
1501 ~ 2100mm ±30mm
>2100mm ±40mm

Imperial

0 ~ 1ft ±0.5in
2ft ~ 3ft ±0.75in
4ft ~ 7ft ±1.0in
> 7ft ±1.5in

Wiring Map: 568B Standard




Example Parts Numbers

Feet		
P/N	Color	Length
BC-6UG001F	Grey	1'
BC-6UK010F	Black	10'
BC-6UK025F	Black	25'

For Part Numbers Not Shown Follow Part Number Key Format



THIRD ANGLE PROJECTION		206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com	
DO NOT SCALE DRAWING	TITLE: Bel Patchcord Assembly, C6 U/UTP		
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.		
DIMENSIONS: INCHES [METRIC]	DRN BY: XYQ	DATE: 05/17/17	
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°	APPD BY: HU	DATE: 05/17/17	
SHEET NO. 1 OF 1	DWG NO. CT999141	REV. A2	