



DATE	REV	ECN	APP'D. BY
10/25/19	A0	-	JME
12/04/19	A1	11483	ADB



PART NUMBER KEY



0/A Length Tolerance:

Metric	
0 ~ 200mm	±10mm
201 ~ 1000mm	±20mm
1001 ~ 1500mm	±25mm
1501 ~ 2100mm	±30mm
>2100mm	±40mm

Imperial	
0 ~ 1ft	±0.5in
2ft ~ 3ft	±0.75in
4ft ~ 7ft	±1.0in
> 7ft	±1.5in

WIRING MAP

P1	P2	Color
1	8	BLUE
2	7	ORANGE
3	6	BLACK
4	5	RED
5	4	GREEN
6	3	YELLOW
7	2	BROWN
8	1	WHITE

TYPICAL PART NUMBERS	
PART NUMBER	LENGTH FEET [METERS]
BC-88RS007F	7 [2.13]
FOR PART NUMBERS NOT SHOWN FOLLOW PART NUMBER KEY FORMAT	



NOTES:

1. EACH CABLE ASSEMBLY INDIVIDUALLY BAGGED
2. WIRE CONSTRUCTION: 28 AWG WIRE, FLAT TELEPHONE, OD 0.01 x 0.34", SILVER/GREY INSULATION
3. CONNECTOR P1: 8P8C MODULAR PLUG, GOLD FLASH ON CONTACTS
4. CONNECTOR P2: 8P8C MODULAR PLUG, GOLD FLASH ON CONTACTS
5. VOLTAGE RATING: 300 V
6. CONDUCTOR RESISTANCE: 8 Ω
7. INSULATION RESISTANCE: 5M Ω

THIRD ANGLE PROJECTION			206 Van Vorst Street Jersey City, NJ 07302 +1 201 432 0463 http://www.belfuse.com
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	TITLE: RJ45 PATCHCORD CABLE WITH 8 POSITION, 8 CONTACT MODULAR PLUGS (REVERSE)		DRN BY: BTS DATE 10/23/19
DIMENSIONS: INCHES [METRIC]	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°		APPD BY: JME DATE 10/23/19
SHEET NO. 1 OF 1	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.		DWG NO. CT999208 REV. A1