



B

B




PIN ASSIGNMENT



NOTES:


1. COMPLIANT WITH DISPLAYPORT 1.2 SPECIFICATION.
2. CONNECTOR COMPONENTS:
TRANSPARENT DUST COVER
INSIDE MOLDING: PE
STRAIN RELIEF MOLDING: 45P PVC, BLACK
OUTSIDE MOLDING: ABS, BLACK
SHELL PLATING: GOLD FLASH
CONTACT: GOLD PLATING
DISPLAY PORT CABLE UL20276 (28AWG(7/0.127TC)
*1P+D.W+AL+MYLAR)*5+28AWG (7/0.127TC)*5C+
AL/MY+D.W+BD+JACKET PVC COLOR: BLACK
OD: .29±.008 [7.3±0.2]
3. ELECTRICAL TESTING:
100% OPEN & SHORT & CONTINUITY WIRE TEST
CONTACT RESISTANCE: 2 OHM(MAX)
INSULATION RESISTANCE: 10M OHM(MIN)
HI-POT TEST: DC 100V/10ms
4. PACKAGING:
ONE CABLE PER BAG



P/N	LENGTH
BC-DD003F	36±0.8 [915±20]
BC-DD006F	72±1.2 [1830±30]
BC-DD010F	120±1.6 [3050±40]



THIRD ANGLE PROJECTION
DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS: INCHES [METRIC]
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ±.005 [0.13] ANGLES ARE ± 1°
SHEET NO. 1 OF 1



bel

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE: DISPLAY PORT MALE TO DISPLAY PORT MALE CABLE

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

DRN BY: JMM	DATE 05/16/19
APPD BY: ADB	DATE 05/29/19
DWG NO. CT999190	REV. A1