




.262 ±.008 [6.65 ± .20]




DATE	REV	ECN	APP'D. BY
12/22/20	A0	RELEASED	ADB
-	-	-	-

Notes:

- Cable:
 - USB 3.1 [34AWG(7/0.06TC)+EAM]*4P+32AWG(7/0.08TC)*2C+26AWG (7/0.16TC)*2C+32AWG(7/0.08TC)*4C+AB (16/10/0.08 85%TC)OD: 4.2MM
 - JACKET COLOR: BLACK.
 - CABLE MARKING: E515987 兄 AWM STYLE 2725 80℃ 30V VW-1 RoHS C1
- Connector P1:
 - USB C MALE 3.1, GOLD FLASH ON SHELL, WITH PCB, BLACK INSULATOR.
- Molded Boot: 45P PVC color Black
- DP M ABS SHELL Color: Black
- TRANSPARENT DUST COVER
- Connector P2:
 - UTCV-9FT With PCB SHELL Gold Plated
- SCREW: #4-40UNC 2.8*58.25MM
- Electrical Test:
 - 100%Test(Open ,Short ,Wire Map)
 - CONTACT RESISTANCE 3 OHM MAX
 - INSULATION RESISTANCE: 10M OHM MIN
 - HI-POT: 300V DC/10 ms
 - RESOLUTION: 1920 * 1200
- PACKAGING: EACH CABLE ASSEMBLY TO BE INDIVIDUALLY BAGGED


Pin Assignment



P/N	LENGTH
BC-VC003F	3 FT ±.79" [915 mm ±20 mm]
BC-VC006F	6 FT ±1.18" [1830 mm± 30mm]
BC-VC010F	10 FT ±1.97" [3050 MM± 50mm]



THIRD ANGLE PROJECTION




DO NOT SCALE DRAWING
DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±.005 [0.13]
ANGLES ARE ± 1°

SHEET NO. 1 OF 1



bel

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE: USB TYPE C MALE 3.1 TO VGA

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF BEL FUSE, INC.

DRN BY:	GL	DATE	12/18/20
APPD BY:	ADB	DATE	12/21/20
DWG NO.	CT999238	REV.	A0