


| DATE     | REV | ECN | APP'D. BY |
|----------|-----|-----|-----------|
| 02/26/18 | A0  | --  | JC        |
|          |     |     |           |



Notes:

- 1) Each cable assembly to be individually bagged.
- 2) 50μ" Gold plating on contacts
- 3) Cable Construction:
  - 28AWG Stranded
  - 4Pr, F/UTP, Type CMR
  - PVC Jacket
- 4) Slimline Snagless Strain Relief
- 5) 100% Transmission Tested for Performance

P/N Key:

BM-R6ASxxxxF

UOM


F = Feet

Color

E = Blue  
K = Black  
N = Green

| Length |      |
|--------|------|
| XXX    | Feet |
| 001    | 1    |
| 003    | 3    |
| 005    | 5    |
| 007    | 7    |
| 010    | 10   |
| 015    | 15   |

Wiring Map: 568B Standard



Example Parts Numbers

| Feet         |       |        |
|--------------|-------|--------|
| P/N          | Color | Length |
| BM-R6ASE001F | Blue  | 1'     |
| BM-R6ASK010F | Black | 10'    |
| BM-R6ASN015F | Green | 15'    |

For Part Numbers Not Shown Follow Part Number Key Format



THIRD ANGLE PROJECTION

DO NOT SCALE DRAWING  
DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE

DIMENSIONS: INCHES [METRIC]

UNLESS OTHERWISE SPECIFIED  
TOLERANCES ARE ±.005 [0.13]  
ANGLES ARE ± 1°

SHEET NO. 1 OF 1

206 Van Vorst Street  
Jersey City, NJ 07302  
+1 201 432 0463  
<http://www.belfuse.com>

TITLE:  
**Bel Patchcord Assembly, C6A F/UTP, 28 awg, CMR**

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF BEL FUSE, INC. AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF BEL FUSE, INC.

|                  |               |
|------------------|---------------|
| DRN BY: TLS      | DATE 02/26/18 |
| APPD BY: JC      | DATE 02/26/18 |
| DWG NO. CT999172 | REV. A0       |