


US Power Supply Cord with IEC Connector C19, straight



Description

- 1 Function:
- Power Cord, Protection class I
- Pin temperature 70 °C
- custom specific versions on request

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data

Ratings UL/CSA	15 A / 125 VAC; 50/60Hz
Allowable Operation Temp.	-40 °C to 70 °C
Degree of Protection	from front side IP 40 acc. to IEC 60529
Protection Class	Suitable for appliances with protection class I acc. to IEC 61140
Material: Housing	black

Connector	C19 acc. to IEC 60320 UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 16A, Protection Class I
-----------	--

All Variants

Connector		cable				Plug					Order Number
Type	V-Lock	Cord Type	Conductor cross section	Length [m]	Color	Type	Country	Standard	Style	Index	
C19		SJT 3x14 AWG	3 x 14 AWG	2.5	black	North America	USA	NEMA 5-15	-	-	6009.5195

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 25 Pcs

Mating Inlets/Plugs

Category / Description

[Appliance Inlet Overview complete](#)



IEC Appliance Inlet C20 or C24, Split panel or screw-on mounting, PCB Terminal	GSP4
IEC Appliance Inlet C20, Screw-on Mounting, Rear Side, PCB Terminal	1601
IEC Appliance Inlet C20, Screw-on Mounting, Front Side, Solder or Quick-connect Terminal	4798
IEC Appliance Inlet C20, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal	4793
IEC Appliance Inlet C20, Snap-in Mounting, Front Side, Solder, Quick-connect or Screw Terminal	1624
Appliance Inlet further types to 6009.5195	...



Appliance inlets/-outlets Overview complete

Plug Coupler IEC C20 / IEC J, Screw-on Mounting

4730

Appliance inlets/-outlets further types to 6009.5195



Plug Overview complete

IEC Plug I, Cord Connector (Rewireable), Straight

0922

Plug further types to 6009.5195



Power Entry Module Overview complete

IEC Appliance Inlet C20 with Line Switch, 2-pole

EC11

0 0 0 0 0

6136

IEC Appliance Inlet C20 with Circuit Breaker TA45

EF11

Power Entry Module further types to 6009.5195



Power Entry Module with line filter Overview complete

EC12, 20 A, prewired, Standard and Medical Version, Quick connect terminals 6.3 x 0.8 mm, Capacitor: X2, Screw, Mounting Front-Side, Power Entry Modules with Filter

EC12

IEC Appliance Inlet C20 with Filter, Circuit Breaker TA45 (recessed)

EF12

C20F, 20 A, prewired, Standard and Medical Version, Solder, quick connect or wires (stranded), Capacitor: X2, Screw, Mounting Front-/Rear-Side, Power Entry Modules with Filter

C20F

Power Entry Module with line filter further types to 6009.5195