

## Series: Cover OG, UHB, UH

Cover for Holder OG (Clip) 5x20, OG (Halter) 5x20, UH, UHB



Share



PDF



2 Variants

[Approvals and Compliances](#)

[CAD](#)

[Microsite Fuseholder](#)

### Description Cover OG, UHB, UH

[Detailed request for product](#)

### Details Cover OG, UHB, UH

[Technical Data](#) [Approvals and Compliances](#) [Dimension](#)

<b>Fuse-Link</b>	5 x 20 mm
<b>Rated Power Acceptance IEC</b>	2.5 W / 10 A @ Ta 23 °C 1.6 W / 10 A depending on the type
<b>Admissible Ambient Air Temp.</b>	-40 °C to 85 °C
<b>Material: Cover</b>	Thermoplastic Transparent UL 94V-0
<b>Storage Conditions</b>	0 °C to 60 °C, max. 70% r.h.

### Short Table of Variants Cover OG, UHB, UH

[Open complete table Cover OG, UHB, UH](#)

Designation	Order Number	A=Most Popular	Free Sample	Distributor Stock Check	...
(all)					
Transparent Cover 1.6 W	0853.9561				...
Transparent Cover 2.5 W	0853.9562				...

Most Popular.

### References / Document Downloads

### References Cover OG, UHB, UH

[Home](#)

[Components](#)

[Input Systems](#)

[Solutions](#)

[Careers](#)

[About SCHURTER](#)

[About Components](#)

[About Input Systems](#)

[About Solutions](#)

[Why SCHURTER](#)

[Our skills](#)

[Products](#)

[References](#)

[Applications](#)

[Stories](#)

[Services](#)

[Affiliates](#)

[Technologies](#)

[Partner](#)

[Job openings](#)

[International](#)

[Sales Partner](#)

[Competences & Quality](#)

[Structure](#)

[Apprenticeship](#)

[Events](#)

[Catalog](#)

[Markets](#)

[Support](#)

[Trainees at SCHURTER](#)

[Press](#)

[Locations](#)

[GTC](#)