

Products → Low Voltage Products and Systems → Connection Devices → Test Blocks Accessories → Test Plugs

General Information

Extended Product Type:	FC4-1
Product ID:	1SNA167927R1000
EAN:	3472591679274
Catalog Description:	FC4-1-RD Test Plugs DIA 4 mm .19 in - Red
Long Description:	— Allows circuit test when associated with the test adapter or when the block is equipped with a test socket, - Soldered connection.

Ordering

Color:	Red
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC169001C0210
Instructions and Manuals:	1SNC169001C0210

Dimensions

Product Net Width:	9.5 mm
Product Net Height:	9.5 mm
Product Net Depth / Length:	75 mm
Product Net Weight:	11 g

Technical

Spacing:	2 mm
Function:	Test Plugs
Rated Current (I_n):	Main Circuit 10 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Suitable For:	C6/8.ST4 D6/8.ST.RS M6/8.ST M6/8.STP RGW6-R1 RGW6-ST-1

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
---------------------------------	---------------------------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225040C1005

Environmental Information: 1SND220073E1000

Instructions and Manuals: 1SNC169001C0210

Classifications

Object Classification Code: X

ETIM 4: EC002255 - Test plug terminal block

ETIM 5: EC002255 - Test plug terminal block

ETIM 6: EC002255 - Test plug terminal block

Container Information

Package Level 1 Units: 10 piece

Package Level 1 Gross Weight: 0.11 kg

Package Level 1 EAN: 3472591679274