

# PC-RG2.5-2



PC-RG2.5-2 Ring lug Lateral Jumper Bar - 2 poles - Orange



## General Information

Extended Product Type	PC-RG2.5-2
Product ID	1SNA519103R0200
EAN	3472599856813
Catalog Description	PC-RG2.5-2 Ring lug Lateral Jumper Bar - 2 poles - Orange
Long Description	- Lateral jumper bar for ring lug terminal block, - Allow the connection of consecutive blocks, - Compatible with RGW terminal block of 9 mm 0.354 in spacing

## Ordering

Color	Orange
Minimum Order Quantity	25 piece
Customs Tariff Number	85369010

## Dimensions

Product Net Width	3.1 mm
Product Net Height	14.1 mm
Product Net Depth / Length	25.8 mm
Product Net Weight	3.02 g

## Technical

Spacing	9 mm
Function	Jumper Bars
Rated Current ( $I_n$ )	Main Circuit 24 A
Rated Voltage ( $U_r$ )	800 V
Power Loss	0.8 W
Insulation Material	Polyamide
Suitable For	RGW2.5 RGW2.5-T

## Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V
Flammability According to UL94	V0

---

## Environmental

---

Ambient Air Temperature	Operation -40 ... +100 °C Storage -40 ... +100 °C
RoHS Status	Following EU Directive 2011/65/EU

---

---

## Certificates and Declarations (Document Number)

---

Declaration of Conformity - CE	1SND225158C1001
Environmental Information	1SND220070E1001
RoHS Information	1SND230547F0201

---

---

## Classifications

---

ETIM 4	EC000489 - Cross-connector for terminal block
ETIM 5	EC000489 - Cross-connector for terminal block
ETIM 6	EC000489 - Cross-connector for terminal block

---

---

## Container Information

---

Package Level 1 Units	25 piece
Package Level 1 Width	55 mm
Package Level 1 Depth / Length	31 mm
Package Level 1 Height	65 mm
Package Level 1 Gross Weight	0.1 kg
Package Level 1 EAN	3472599856813
Product Packing Type	Box

---

---

## Categories

---

Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories → Lateral Jumper Bars

