



Actual

**Catalog Number:** 13713B  
**Product ID:** 7TAA131850R0047  
**UPC Number:** 78621070171  
**EAN Number:** 05414363111474  
**Status:** A

Die for 14 Ton 13100A or 15 Ton TBM15i Hydraulic Tool for Crimping 2200 Series Dragon Tooth Terminals

- Application Tools: 13100A, TBM15I

### North American Specifications (UNSPSC)

UNSPSC	27112820 Lug crimping tool dies
IGCC	2427 Lug crimping tool dies
Brand Name	Dragon Tooth
Type	Die
Application	Crimping Dragon Tooth terminal for magnet wire
Material	Alloy Steel
Color	Silver

### European Specifications (ETIM)

ETIM	EC001282 Insert for crimp tool cable lugs, cable end sleeves, screen connection
Application	Insulated varnish wire-cable lugs and connectors
AWG-range	10 - 1/0
Compression shape	Trapezoid compression

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	4x4x3
Weight Uom	100 lbs. per 100

### Documents / Support Tools

Instruction Sheet	TA02760-TB2
-------------------	-------------

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)