



Representative

Catalog Number: 14RBC-38
Product ID: 7TAI029470R0028
UPC Number: 78621081684
EAN Number: 05414363935599
Status: A

Vinyl-Insulated Heavy-Duty Ring Terminal, Length 1.34 Inches, Width 0.63 Inch, Maximum Insulation 0.20, Bolt Size 3/8 Inch, Wire Range 16-14 Heavy Duty AWG, Color Green, Copper, Tin Plated

- Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
- Application Tools: WT2000, ERG4001
- Alternate Package Qty: RBC797

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Type	Vinyl Insulated Heavy-Duty Ring Terminal
Special Features	Funneled Barrel Entry, Deep Internal Serrations, Brazed or overlapping seams.
Standard	UL E9809
Wire Size	16-14 AWG
Voltage Rating	600 V
Material	Copper
Color	Green

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PVC
Colour insulation	Other
Reel packaging	N
Sleeve form	Short
AWG-range	16-14
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	12.5x10.5x8.25
Weight Uom	1.88 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com