



Flexible Conduits & Fittings

T&B Catalog Number:

BUAV-M207-UL

UPC Number:

78620994777

Status:

Active

Description:

FIXPLus 45 degree black elbow, material - polyamide 6. Thread type - metric, thread size - M20 x 1.5, conduit size NW - 17

Application

For cable protection systems in a wide range of applications

Excellent fire characteristics allow application in public buildings such as hospitals, hotels, airports, train and subway stations, shopping centers, etc.

Characteristics

Extremely high impact resistance

Vibration resistant connection to PMAFLEX conduits

Easy installation

High conduit pull-out strength

Very good chemical properties

Free from halogens and cadmium

Fits conduit profile coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	Metric
Compatible With	PMA FLEXPLus

Dimension Information

Fits to Conduit Size (NW)	17
Fits to Conduit Size (metric)	20
Fits to Conduit Size (inches)	1/2
Thread Size (Metric)	M20 x 1.5

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Specifications

NEMA Rating NEMA 6P stat./ NEMA 6 dyn.

IP Ratings

IP Rating IP68 stat. / IP67 dyn.

Packaging

T&B Inner Pack	50
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	0.35 lbs. Each

Application Support

PMA Reference Guide Available on Website

Product Overview-FIXPLus Fittings Available on Website

Product Overview-PMAFIX Connectors Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 174370

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com