



Actual

Catalog Number: 250-G
Product ID: 7TCA296220R0170
UPC Number: 78621027066
EAN Number: 05016947003870
Status: A

Standard Cable Gland, M16 Metric Thread, 10mm Thread Length, 25mm Gland Depth, 22mm Gland Diameter, 19mm Across Flats Dimension, 7-10mm Cable Diameter Range, Polyamide 6.6 with Nitrile Rubber Seal, IP66, Grey

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Type	Standard Cable Gland
Application	Provide Strain Relief and Connection for Conduit Systems
Size	M16
Conductor Range	7.0 to 10.0 mm
Material	Polyamide/Nylon 6.6 with Nitrile Rubber Seal
Color	Gray
Insulation	IP66

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	Metric
Nominal thread size metric/PG	16
Thread length	11mm
Wrench width	19mm
Hexagon angular dimension	22mm
Suitable for cable diameter	7-10mm
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Glass-fibre reinforced	N
Degree of protection (IP)	IP66
Shock resistant	N
Colour	Dark grey
RAL-number	7030
Bend radius protection/trumpet flare	N
With locknut	N
Model	Straight
Flat cable coupling	N
Strain relief	N
Operating temperature	-20-+90°C
Explosion-tested version	N
For Ex-zone gas	None
For Ex-Zone dust	None
EMC-version	N

Packaging

Outer Quantity	100
Outer Dimensions (inches)	1x1x1
Weight Uom	0.04 lbs. Each

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.

ABB Installation Products Technical Support
 MS 3B-50

Hours: 7AM - 6PM CDT
 Monday-Friday



Memphis, TN 38120
www.tnb.com

860 Ridge Lake Blvd.
Memphis, TN 38120

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com