



## Flexible Conduits & Fittings

### T&B Catalog Number:

BVIR-M508

### UPC Number:

78620995049

### Status:

Active

### Description:

PMAFIX black female thread adapter with metric threads. Material - polyamide 6, thread size - M50 x 1.5, nominal width/ conduit size - 48.

### Application

For use in machine, vehicle and traction building

### Characteristics

Very high impact resistance

Vibration-proof connection to PMAFLEX conduits

High conduit pull-out strength

Very good chemical properties

Free from halogens and cadmium

Fits both conduit profiles - Fine (T) and coarse (G)

### General

Material Polyamide 6

Color Black

Thread Type Metric

Suitable for Use With PMAFLEX, PMA Smart Line

### Dimension Information

Fits to Conduit Size (NW) 48

Fits to Conduit Size (metric) 50

Fits to Conduit Size (inches) 1 1/2

Thread Size (Metric) M50 x 1.5

### Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

### Specifications

3dmodel Available on Website

### IP Ratings

IP Rating IP68 stat. / IP67 dyn. On conduit side

### Packaging

T&B Inner Pack 10

Package in Units 100

T&B Sold in UOM Each

T&B Weight Per UOM 0.11 lbs. Each

### Application Support

PMA Reference Guide Available on Website

Product Overview-PMAFIX Connectors Available on Website

PMAFIX Connectors-Safety and Sealing Systems Available on Website

Systems

### Certifications

RoHS Compliance Yes

## Certifications



### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)