



Thin-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

CPO500-S-C

UPC Number:

78620999793

Status:

Active

Description:

Heat Shrink Tubing, Striped, 1/2 Inch, Length 100 Foot

Features

Flame-retardant, cross-linked polyolefin.

Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C;
MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637;
DEF STAN 59-97, Issue 3, Type 2a

General

Style	CPO Series Non-Lined
Color	Green/Yellow Striped
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

Dimension Information

Length (feet)	100
Minimum Expanded I.D. (inches)	0.5
Maximum Recovered I.D. (inches)	0.25
Nominal Recovered Wall (inches)	0.025
Cable Range	6 - 1 AWG

Specifications

Shrink Temperature	120°C
--------------------	-------

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	1.9 lbs. Each

Application Support

Specifications	Available on Website
Overview	Available on Website

Notes

Order multiple is for 4 ft. sticks is 25 sticks. Order multiple for reels is 1 reel. When ordering standard package, order by package not feet.

UL Recognized File Number E137759 and CSA Certified. Clear material not UL Recognized.

Larger diameters available upon special request; consult Customer Service.

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com