



Sta-Kon®

Ring Terminal
T&B Catalog Number:


F10711
 78621082966
 Active

UPC Number:
Status:
Description:

Non-Insulated Tubular Ring Terminal, Length 1.37 Inches, Width .55 Inches, Bolt Hole 1/4 Inch, Wire Range 4/4AN, Copper, Tin Plated

Features

These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).



General

Insulation Type	Non-Insulated - Tubular
Terminal Series	F
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	4
Stud Size	1/4

Dimension Information

Stock Thickness	.04
A (inches)	1.37
B (inches)	.55
C (inches)	.30
M (inches)	1.07

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
MIL Specification	MS-20659-111

Tooling

Tool Charts	Available on Website
Application Tools	WT115A, TBM6, TBM6S, WT3185
Recommended Tool	ERG4008

Packaging

T&B Order Multiple	100
T&B Inner Pack	100
Package in Units	1000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000168
Overview	Available on Website
Wire Guide Tables	Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com