



T&B[®]

Liquidtight Flexible Cord & Cable Fittings T&B Catalog Number:

UPC Number: 2268
78621002268
Status: Active
Description:

Liquidtight Strain Relief Cord Connector, 1/2 Inch, 90 Degree Bend, Meets Coast Guard CG293, Cord Range 0.250 to 0.375 Inch, Malleable Iron

Application

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).
Meets Coast Guard CG293

General

Material Malleable Iron

Dimension Information

Hub Size (inches) 1/2
Dimension A (inches) 1 5/32
Dimension B (inches) 1 23/32
Dimension C (inches) 5/8
Cord Range (inches) .250-.375

Specifications

3dmodel Available on Website
Temperature Rating 105 C

Packaging

T&B Inner Pack 25
Package in Units 50
T&B Sold in UOM Each
T&B Weight Per UOM 23 lbs. per 100

Application Support

Product Overview Available on Website
Specifications Available on Website
Portable Cord Selection Table Available on Website

Notes

Suitable for use in hazardous locations where general purpose equipment is specifically permitted by NEC 501-4(b).

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com