



Actual

**Catalog Number:** TY15X15NPG6  
**Product ID:** 7TAA104040R0024  
**UPC Number:** 78621095695  
**EAN Number:** 05415022310344  
**Status:** Obsolete  
**Replacement Catalog:** TYD15X15NPG6

Wiring Duct Narrow Slot 1-1/2 Inch X 1-1/2 Inch Rigid PVC Gray

- Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enable same duct for multiple applications.

### North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Wiring Duct
Special Features	Smaller, higher number of fingers for more concise harnessing. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
Width	1.75
Depth	1.60
Length	6
Mounting Holes	Yes
Material	Rigid PVC
Color	Gray

### European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	40.6mm
Width	44.5mm
Length	1829mm
Halogen free	Y
Type of fastening	Adhesive film
With cover	N
Colour	Light grey

### Packaging

Inner Quantity	6
Outer Quantity	120
Outer Dimensions (inches)	73x9.25x6.75
Weight Uom	17.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000181

For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)