



Representative

Catalog Number: 54011
Product ID: 7TAH007530R0013
UPC Number: 78621054011
Status: Active

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size 3/0 AWG, Die Set 15CA49R, , Die Color Code Orange

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
- Application Tools: 13100A, TBM15I, TBM14M

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Color-Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Standard	UL E9809
Conductor Range	3/0 AWG
Material	Copper
Finish	Tin-Plated
Color	Orange
Voltage Rating	Max 35kV
Insulation	None

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Sleeve form	Long
Material	Copper
Insulation	None
Voltage row	Up to 35kV

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	12.2x6x3.4
Weight Uom	6.88 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00607-TB2

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com