



Representative

Catalog Number: 54482
Product ID: 7TAH007200R0047
UPC Number: 78621054482
EAN Number: 05414363143963
Status: A

Copper Two-Hole High Voltage Lug, Long Barrel, Blind End, Max 15kV, Wire Size 350 kcmil, 1/2 Inch Bolt Size, 1-3/4 Inch Hole Spacing, Tin Plated, Die Code 71R, Die Color Code Red Rounding Die

- Recommended for up to 15KV applications, installed with standard T&B tools with special rounding dies.
- The rounding die overlapped compressions provide a smooth round surface. This combined with the tapered barrel ends, addresses the controlling of potentially damaging electrical stresses of high voltages.
- High conductivity wrought copper, tin plated. Cable Area Clearly Identified on Lug.

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel
Special Features	Recommended for up to 15KV applications, installed with standard T&B tools with special rounding dies.
Standard	UL E9809
Cable Size	350 kcmil
Stud Size	1-3/4 in
Number Of Holes	2
Voltage Rating	35kV
Insulation	None
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	50
Outer Dimensions (inches)	24.5x6.8x4.3
Weight Uom	38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Instruction Sheet	TA00606-TB2

For further technical assistance, please contact us...

860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com