



Representative

**Catalog Number:** 54858BE  
**Product ID:** 7TAH007800R0024  
**UPC Number:** 78621089800  
**EAN Number:** 05415022246032  
**Status:** A

Copper Two-Hole Lug, Long Barrel, Blind End, Max 35kV, Wire Size #1 AWG, 5/16 Inch Bolt Size, 7/8 Inch Hole Spacing, Tin Plated, Die Code 37, Die Color Code Green

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Type	Long Barrel
Standard	UL E9809
Cable Size	1 AWG
Stud Size	5/16 in
Number Of Holes	2
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Green

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Inner Quantity	20
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	200
Outer Dimensions (inches)	12.2x6x3.4
Weight Uom	6.5 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	TDS000519
Instruction Sheet	TA01025-TB2

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

ABB Installation Products Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)