



Representative

**Catalog Number:** 54859BEBS  
**Product ID:** 7TAH007890R0829  
**UPC Number:** 78621095501  
**Status:** Active

Copper Two-Hole Lug, Long Barrel - Bell Shaped End, Blind End, Max 35kV, Wire Size 1/0 AWG, 1/4 Inch Bolt Size, 5/8 Inch Hole Spacing, Tin Plated, Die Code 42, Die Color Code Pink

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel - Bell Shaped End
Standard	UL E9809
Cable Size	1/0 AWG
Stud Size	1/4 Inch
Number Of Holes	2
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Pink

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	2

### Packaging

Inner Quantity	5
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	25
Outer Dimensions (inches)	7.62x6.62x3.5
Weight Uom	8.7 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)