



Representative

Catalog Number: 54929BEUB
Product ID: 7TAH007990R1525
UPC Number: 78621084583
Status: Active

Copper One-Hole Lug, 90 Degree Long Barrel, Blind End, Max 35kV, Wire Size #8 AWG , #10 Bolt Size, Tin Plated, Die Code 21, Die Color Code Red

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Long Barrel 90 Degree Bend
Standard	UL E9809
Cable Size	#8 AWG
Stud Size	#10
Number Of Holes	1
Voltage Rating	Max 35kV
Insulation	None
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
Insulated	N
With sight-hole	N
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	10
Inner Dimensions (inches)	3.25x2.75x2.25
Outer Quantity	50
Outer Dimensions (inches)	7.62x6.62x3.5
Weight Uom	1.6 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com