

Catalog Number: 58168NT06B
Product ID: 7TAH007990R1702
UPC Number: 78620994265
Status: A

Copper One-Hole Lug, Standard Barrel - Narrow Tongue, Bottom Stacking, Peep Hole, Max 35kV, Wire Size 250 Flex, 1/2 Inch Bolt Size, Tin Plated, Die Code 66, Die Color Code White

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel - Narrow Tongue
Cable Size	250 AWG
Stud Size	1/2 in
Number Of Holes	1
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	White

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	Y
Insulated	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Inner Quantity	5
Inner Dimensions (inches)	4x3x4
Outer Quantity	50
Outer Dimensions (inches)	21.5x8.5x3.43
Weight Uom	14.5 lbs. per 100

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com