

# AL21/U094/A/000620



ALOK A INT 15/16UNEF



## General Information

Extended Product Type	AL21/U094/A/000620
Product ID	7TCA296000R0713
EAN	5020963036323
Catalog Description	ALOK A INT 15/16UNEF
Long Description	Connector Conduit Fitting, Straight, Conduit Size 21, 15/16 Inch Connector UNEF Thread, Swivel Internal Thread, Black

## Ordering

EAN	5020963036323
Minimum Order Quantity	10 piece
Customs Tariff Number	3917400090

## Dimensions

Product Net Weight	18.144 g
--------------------	----------

## Container Information

Package Level 1 Units	10 piece
Package Level 2 Units	200 piece
Package Level 2 Width	355.6 mm
Package Level 2 Height	152.4 mm
Package Level 2 Depth / Length	355.6 mm

## Additional Information

Brand / Label	Adaptaflex
Cable Entry Position	15/16 Inch UNEF Thread
Color	Black
Function	For Insertion into Threaded Entries or Knockout to Connect Conduit
Material	Polyamide/Nylon 6.6
Product Main Type	ADAPTAFFLEX FLEXIBLE CABLE PROTECTION
Product Name	plastic fitting for conduit
Product Type	Conduit Fitting with UNEF Threads
UPC	786210279909

---

## Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	AL21/U094/A/000620
Instructions and Manuals	AL21/U094/A/000620

---

---

## Classifications

---

ETIM 6	EC001176 - Screw connection for corrugated plastic hose
ETIM 7	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

---

---

## Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

