



Flexible Conduits & Fittings

T&B Catalog Number:

BUAV-N098-UL

UPC Number:

78620994789

Status:

Active

Description:

FIXPLus 45 degree black elbow, material polyamide 6. Thread type - NPT threads, thread size - 2 in., conduit size NW - 48.

Application

For cable protection systems in a wide range of applications

Excellent fire characteristics allow application in public buildings such as hospitals, hotels, airports, train and subway stations, shopping centers, etc.

Characteristics

Extremely high impact resistance

Vibration resistant connection to PMAFLEX conduits

Easy installation

High conduit pull-out strength

Very good chemical properties

Free from halogens and cadmium

Fits conduit profile coarse (G)

General

Material	Polyamide 6
Color	Black
Thread Type	NPT
Compatible With	PMA FLEXPLus

Dimension Information

Fits to Conduit Size (NW)	48
Fits to Conduit Size (metric)	50
Fits to Conduit Size (inches)	1 1/2
Thread Size (NPT)	2

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Specifications

NEMA Rating NEMA 6P stat./ NEMA 6 dyn.

IP Ratings

IP Rating IP68 stat. / IP67 dyn.

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	80
T&B Sold in UOM	Each
T&B Weight Per UOM	0.02 lbs. Each

Application Support

PMA Reference Guide	Available on Website
Product Overview-FIXPLus Fittings	Available on Website
Product Overview-PMAFIX Connectors	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
E 174370

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com